

# Sample Actuator Kit *Curve*® plugged 3920M

CompActive


## Read instructions before use!

- General function: as long as the button is pushed the actuator is heated and the actuation is initiated
- Before first usage remove battery protector
- Use fixation area to hold with fingers, press on a table or clamp
- Push button for max. 4 s , release when actuation slows down
- Voltage is limited to 3.7 V due to battery properties → no risk of electrical shock

Li-ion Battery 3.7 V / Size 18650

- **Observe safety notes on Li-ion batteries**
- Chargeable with compatible Li-ion battery chargers for Li-ion batteries size 18650
- Remove battery by pushing from below

Actuator *Curve*® plugged 3920M



rechargeable Li-ion Battery 3.7 V 2600 mAh



Battery protector

non-latching button

